* PULSAFEEDER®

The Pulsatron Series HV designed for high viscosity applications for precise and accurate metering control. The Series HV offers manual control over stroke length and stroke rate as standard with the option to choose between 4-20mA and external pace inputs for automatic control.

Five distinct models are available, having pressure capabilities to 150 PSIG (10 BAR) @ 12 GPD (1.9 lph), and flow capacities to 240 GPD (37.9 lph) @ 80 PSIG (5.6 BAR), with a turndown ratio of 100:1. Metering performance is reproducible to within \pm 2% of maximum capacity.

Features

- Automatic Control, available with 4-20mADC direct or external pacing, with stop function.
- Manual Control by on-line adjustable stroke rate and stroke length.
- Auto-Off-Manual switch.
- Highly Reliable timing circuit.
- Circuit Protection against voltage and current upsets.
- Panel Mounted Fuse.
- Solenoid Protection by thermal overload with autoreset.
- Water Resistant, for outdoor and indoor applications.
- Indicator Lights, panel mounted.
- Guided Ball Check Valve Systems, to reduce back flow and enhance outstanding priming characteristics.
- Viscosities to 20,000 CPS.

Controls



Manual Stroke Rate

Turn-Down Ratio 10:1

Manual Stroke Length

Turn-Down Ratio 10:1

4-20mADC Direct or External Pacing with Stop

Automatic Control

Operating Benefits

- Reliable metering performance.
- Rated "hot" for continuous duty.
- High viscosity capability.



Aftermarket

- KOPkits
- Gauges
- Dampeners
- Pressure Relief Valves
- Tanks
- Pre-Engineered Systems
- Process Controllers (MicroVision)





PULSAiron[®] Series HV Electronic Metering Pumps



Series HV

Specifications and Model Selection

>P									
MODEL		LVB3	LVF4	LVG4	LVG5	LVH7			
Capacity	GPH	0.50	1.00	2.00	4.00	10.00			
nominal	GPD	12	24	48	96	240			
(max.)	LPH	1.9	3.8	7.6	15.1	37.9			
Pressure	PSIG	150	150	110	110	80			
(max.)	BAR	10	10	7	7	5.6			
Connections:	Tubing	(S) .50" I.D. X .75" O.D38" I.D. X .50" OD (LVB3 & F4 only) (S & D) .50" I.D. X .75" O.D. (LVG4,G5 & H7 only)							

Engineering Data

Pump Head Materials Available: GFPPL PVC

Diaphragm: PTFE-faced CSPE-backed

Check Valves Materials Available:

Seats/O-Rings: PTFE

CSPE Viton

Balls: PTFE 316 SS

Fittings Materials Available: GFPPL

PVC

Injection Valve & Foot Valve Assy: Same as fitting and check valve

selected

Tubing: Clear PVC

White PE

Important: Material Code - GFPPL=Glass-filled Polypropylene, PVC=Polyvinyl Chloride, PE=Polyethylene, PVDF=Polyvinylidene Fluoride, CSPE=Generic formulation of Hypalon, a registered trademark of E.I. DuPont Company. Viton is a registered trademark of E.I. DuPont Company. PVC wetted end recommended for sodium hypochlorite.

Engineering Data

Reproducibility: +/- 2% at maximum capacity

Viscosity Max CPS: 20,000 CPS

Stroke Frequency Max SPM: 125
Stroke Frequency Turn-Down Ratio: 10:1
Stroke Length Turn-Down Ratio: 10:1

Power Input: 115 VAC/50-60 HZ/1 ph 230 VAC/50-60 HZ/1 ph

Average Current Draw:

@ 115 VAC; Amps: 1.0 Amps

@ 230 VAC; Amps: 0.5 Amps @ 230 VAC

Peak Input Power: 300 Watts
Average Input Power @ Max SPM: 130 Watts

Custom Engineered Designs – Pre-Engineered Systems





Pre-Engineered Systems

Pulsafeeder's Pre-Engineered Systems are designed to provide complete chemical feed solutions for all electronic metering applications. From stand alone simplex pH control applications to full-featured, redundant sodium hypochlorite disinfection metering, these rugged fabricated assemblies offer turn-key simplicity and industrial-grade durability. The UV-stabilized, high-grade HDPE frame offers maximum chemical compatibility and structural rigidity. Each system is factory assembled and hydrostatically tested prior to shipment.

Series HV Dimensions (inches)									
					Shipping				
Model No.	Α	В	С	D	Weight				
LVB3	5.4	9.3	9.5	7.5	13				
LVF4	5.4	10.8	10.8	7.5	18				
LVG4	5.4	9.5	10.6	7.5	18				
LVG5	5.4	10.8	10.8	7.5	18				
LVH7	6.1	11.5	11	8.2	25				

NOTE: Inches X 2.54 = cm







www.pulsatron.com



sales@novatech-usa.com www.novatech-usa.com Tel: (866) 433-6682 Fax: (866) 433-6684 Tel: (281) 359-8538 Fax: (281) 359-0084



EMP033 B15

**PULSAFEEDER

27101 Airport Road Punta Gorda, FL 33982 Phone: ++1(941) 575-3800 Fax: ++1(941) 575-4085